

FEATURES

- Filament Lamp is a well-established bulb
- History speaks for its self - this is one of the most reliable bulbs
- The lighting provides an excellent colour rendition
- If needed, the bulb could be dimmed easily
- The light bulb wire is easy to installation

BA9s Indicator Light, Clear, 24 V, 83 mA, 10000h

RS Stock No.: 105-102



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

It is interesting how the bulb industry has changed during the last two centuries. Even though they are great light bulbs available on the market, there is still a requirement for Filament Bulbs lighting that brings reliability and a bit of history.

General Specifications

Lamp Base	BA9s
Lamp Size	T3 ¼
Lens Colour	Clear
Luminosity	6.3 lm
Life hours	10000h
Filament Type	Vacuum Type
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	24V
Current Rating	83mA

Mechanical Specifications

Diameter	10.5mm
Length	29mm


Approvals

Compliance/Certifications

RoHS



DRAWING - 1



Unit : mm

1. Structure	Bulb Type	T3 1/4 Clear
	Bulb Diameter	Ø10.5Max.
	Length	29.0Max
	Base Type	Ba9s.
2. Design Characteristics	Voltage	24V
	Amperage	83mA±10%
	Filament Type	Vacuum type
	Luminous Flux	6.3Lm±20%
	Life Hours	10,000Hrs