

FEATURES

- Voltage rating of 30V
- Current rating of 67mA
- 10000 hours lifetime

BA9s Indicator Light, Clear, 30 V, 67 mA, 10000h

RS Stock No.: 105-146



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

It is interesting how the bulb industry has changed during the last two centuries. Even though they are great light bulbs available on the market, there is still a requirement for Filament Bulbs lighting that brings reliability and a bit of history.

General Specifications

Lamp Base	BA9s
Lamp Size	T3 ¼
Lens Colour	Clear
Luminosity	6.3lm
Life hours	10000h
Filament Type	Vacuum Type
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	30V
Current Rating	67mA


Mechanical Specifications

Diameter	10.5mm
Length	29mm

Approvals

Compliance/Certifications	RoHS
---------------------------	------



RS Stock No.	105146	
<i>DRAWING - I</i>		
		
Unit : mm		
1. Structure	Bulb Type	T3 1/4 Clear
	Bulb Diameter	Ø10.5Max.
	Length	29.0.Max
	Base Type	Ba9s.
2. Design Characteristics	Voltage	30V
	Amperage	67mA±10%
	Filament Type	Vacuum type
	Luminous Flux	6.3Lm±20%
	Life Hours	10,000Hrs