MALLORY Mallory Sonalert Products Inc.	Part #	AST0927MW-03Q
Sales Outline Drawing	Revision	A

Specifications:

Oscillation Frequency (Hz)	2700
Operating Voltage (Vp-p)	2 ~ 5
Rated Voltage (Vp-p)	3

Current Consumption Max. (mA) 90 at Rated Voltage Sound Pressure Level (dB/min) 90 at 10cm at Rated Voltage

Coil Resistance (Ω) 16 ± 3 Operating Temperature ($^{\circ}$ C) -30 ~ +70 Storage Temperature ($^{\circ}$ C) -40 ~ +85 Type of Connection Terminal SMD


Housing LCP plastic resin (Color : Black)
Weight (Grams) 0.8

Condition by reflow soldering (°C) 250 ± 5 / within 10 sec Condition by hand soldering (°C) 350 ± 20 / within 5 sec

Options For other options contact factory

Dimensions: (units: mm)

RoHS Compliant



Packaging:

Parts are supplied on cut tape.