

R 1/4" DRIVE METRIC 6-POINT SOCKETS | R.5,5



Norm :

NF ISO 2725-1, NF ISO 1711-1, ISO 2725-1, ISO 1711-1, DIN 3124, ASME B107.5

Description

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.
- Available as sets on metal rack (Ref R.40E).

Information

A [mm]	5,5
d [mm]	11,2
d1 [mm]	8,8
L [mm]	22
L1 [mm]	4,8
[g]	8,40

