

## **TRANSMITTER**

### **Min Operating Voltage**

6 VDC

### **Max Operating Voltage**

48 VDC

### **Working Current**

<200mA

### **Working Frequency**

4KHz

### **Max Operating Temp**

50°C

### **Max Storage Temp**

70°C

### **Max Operating Relative humidity**

80% (Non-condensation)

### **Max Storage Relative humidity**

80% (Non-condensation)

### **Altitude**

<2000m

## **RECEIVER**

### **Power Supply**

2 X 1.5V AAA

### **Working Current**

When not signal be detected <15mA

### **Power Consumption When Power Off**

<10uA

### **Max Operating Temp**

50°C

### **Max Storage Temp**

70°C

### **Max Operating Relative humidity**

80% (Non-condensation)

### **Max Storage Relative humidity**

80% (Non-condensation)

### **Altitude**

<2000m