





未注公差/General tolerances(mm)		0.1/10	
0	>3	>5	>180
~	~	~	~
3	6	10	30
±0.12	±0.18	±0.22	±0.26
		±0.31	±0.37
		±0.57	±0.80
		±0.93	±1.09
		±1.15	±1.60
		±2.20	±2.50
			>500
			0.1/10
			±7



UL 标准/UL Standard:	B	C	D
额定电压/电压/Rated Voltage(V)/Current(A)	600/12	600/12	600/5
EC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/ Pollution Degree	III/3	/	/
额定电压/电流/Rated Voltage(V)/Current(A)	800/6.3	/	/
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	8.0	/	/
螺栓扭矩/Torque Tightening(N·m/Lb.in)	M3, 0.5/4.43		
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm²/AWG)	0.2~4.0/26~10		
间距/Pitch(mm)/线数范围/Poles	8.20		
剥线长度/Stripping length(mm)	8-9		
使用温度范围/Operating Temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		
标准颜色编号/Standard color number:	/		
PANTONE /RAL	/		

MATERIAL: SURFACE:

MAT NO.: /
STATUS: /
APPD: Lj GL 2020.04.03
CHKD: Mao J 2020.04.03
DRT: LIN 2007.09.30

NAME: **DEGSON** 宁波高松电子有限公司
NINGBO DEGSON ELECTRICAL CO., LTD

DRAWING NO.: PC4-HE-C01
SCALE: 1:1
SHEET 1/1

ITEM	NAME OF PART	MATERIAL	NOTES	REV	ECN	DESCRIPTION	DRT	DATE
6	Clamp	Copper alloy	M3/Ni Plated					
5	Brass Cage	Copper alloy	Ni Plated					
4	Spring	Copper alloy	Ni Plated					
3	Screw	Copper alloy	M3/Ni Plated					
2	Body Housing	PA66	UL94V-0					
1	Fuse Housing	PA66	UL94V-0					