

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643340100](#)
Status: **Active**
Overview:
Description: 2.50mm, 3.70mm CMC Header, Right-Angle, 32 Circuits, 1 Port, Black

General

Product Family	PCB Headers
Series	64334
Application	Automotive, Board-to-Board, Wire-to-Board
Comments	Coding: Black
Overview	cmc_connectors
Product Name	CMC
UPC	883906844431

Physical

Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Resin	Nylon Alloy
Net Weight	28.860/g
Number of Rows	4
Orientation	Right Angle
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Solder or Weld

Electrical

Current - Maximum per Contact	12.0A, 2.5A
Voltage - Maximum	14V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	025
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-64334-001-001
Packaging Specification	PK-64334-001-001
Sales Drawing	SD-64334-100-005

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

China RoHS

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[64334](#) Series

Mates With

CMC Receptacle Housing [643193211](#)

Use With

[64322](#) CP 0.6, [64323](#) CP 1.5 Terminal,
[643191201](#) Wire Cap, [64325](#) Blind Plugs

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION