

## FLEXIBLE FITTING



### Specifications

Connection 1	Female 12 mm
Connection 2	Female 17 mm
Length	30cm
Material	Stainless steel (braided)
Maximum Working Pressure	10bar
Operating Temperature Range	80°C

### Flexible supply hoses for sanitary installations

Range of flexible pressure supply hoses for sanitary installations with stainless steel braid with an internal diameter of 9 mm. Offered with various types of connectors, and in two different lengths for certain models.

### Knob Operated Taps & Mixer Taps

Brass units manufactured to BS5412 and chrome plated to BS1224

Handles are clearly marked for hot and cold recognition

Operating pressure range: 0.1 to 10 bar

Max operating temperature: 80°C