

RoHS Reach Halogen Free Pb Free

Applications	Commercial Grade
Feature	No Directivity Multilayer Shield Magnetic Shield Ferrite Core
Series Type	MLF
Status	Production
Brand	TDK



	Size
Length(L)	1.60mm ±0.15mm
Width(W)	0.80mm ±0.15mm
Thickness Height	0.80mm ±0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.

Electrical Characteristics			
Inductance	560nH ±10% at 25MHz		
Rated Current (L Change) [Typ.]			
Rated Current (L Change) [Max.]	100mA		
Rated Current (Temperature Rise) [Typ.]			
Rated Current (Temperature Rise) [Max.]			
DC Resistance [Typ.]	550mΩ		
DC Resistance [Max.]	1.05Ω		
Self Resonant Frequency [Min.]	170MHz		
Self Resonant Frequency [Typ.]	230MHz		
Q [Min.]	15 at 25MHz		
Q [Typ.]	30 at 25MHz		

Other			
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C		
Caldarian Mathad	Reflow		
Soldering Method	Iron Soldering		
AEC-Q200	NO		
Packing	Punched (Paper)Taping [180mm Reel]		
Package Quantity	4000pcs		
Weight	0.004g		


[!] Images are for reference only and show exemplary products.


[!] This PDF document was created based on the data listed on the TDK Corporation website.


 $^{! \ \}mbox{All specifications}$ are subject to change without notice.


RoHS Reach Halogen Free Pb Free

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)










[!] Images are for reference only and show exemplary products.


[!] This PDF document was created based on the data listed on the TDK Corporation website.

[!] All specifications are subject to change without notice.

RoHS Reach Halogen Free Pb Free

Associated Images





[!] Images are for reference only and show exemplary products.

[!] This PDF document was created based on the data listed on the TDK Corporation website.

 $^{! \ \}mbox{All specifications}$ are subject to change without notice.