

Bocube

Enclosures, ABS, single-coloured



B 100809 ABS 7035
Order no.: 96032135

* = Available on request.

Characteristics

Colour of enclosure group
Light grey, similar to RAL 7035

Colour of enclosure group
Light grey

Protection class
IP 66, 68 - 1,2m (2 hours)

Enclosure Material

ABS or PC UL 94 V0 (material is suitable for outdoor use; f1-listing according to UL 746C)

PU seal, foamed; for details please see Technical Information

Scope of delivery

Lid and base, hinged quick-release catches

Note

Material shrinkage may result in ABS enclosures being approx. 0.1 - 0.25 % larger.

Important!


To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

Dimensions

Dimensions
113 x 80 x 90 mm

Product drawing



Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary
Product drawing in PDF format: 96032135 B-100809-ABS-7035.pdf (185.0 KB)
Product drawing in DXF format: 96032135 B-100809-ABS-7035.dxf (3.6 MB)
Drawing for mechanical processing: 96032135 B-100809-ABS-7035-G.dxf (3.0 MB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Works Test Certificates

688 WPZ-Bocube-PC-V0 DE.pdf (184.6 KB)
689 WPZ-Bocube-ABS DE.pdf (165.1 KB)
689 WPZ-Bocube-ABS EN.pdf (160.3 KB)
688 WPZ-Bocube-PC-V0 EN.pdf (179.1 KB)

Product information

Bocube GB.pdf (1.9 MB)
Highlights Bocube.pdf (3.8 MB)

Matching accessories



Hinged quick-release catches (Set), polycarbonate UL 94 V0 or ABS

96330100	B SC 08 ABS 3000	For B 0808.., B 1008.., B 1408.., B 1808..	Flame red
96330102	B SC 08 ABS 5002	For B 0808.., B 1008.., B 1408.., B 1808..	Ultramarine blue
96330109	B SC 08 ABS 6029	For B 0808.., B 1008.., B 1408.., B 1808..	Mint green
96330104	B SC 08 ABS 7024	For B 0808.., B 1008.., B 1408.., B 1808..	Graphite grey
96330105	B SC 08 ABS 7035	For B 0808.., B 1008.., B 1408.., B 1808..	Light grey
96330103	B SC 08 ABS 1023	For B 0808.., B 1008.., B 1408.., B 1808..	Traffic yellow



Hand-operated hinged catch (set), polycarbonate UL 94 V0 or ABS

96930100	B SC HB 08 ABS 3000	For B 0808.., B 1008.., B 1408.., B 1808..	Flame red
96930102	B SC HB 08 ABS 5002	For B 0808.., B 1008.., B 1408.., B 1808..	Ultramarine blue
96930109	B SC HB 08 ABS 6029	For B 0808.., B 1008.., B 1408.., B 1808..	Mint green
96930104*	B SC HB 08 ABS 7024	For B 0808.., B 1008.., B 1408.., B 1808..	Graphite grey
96930105*	B SC HB 08 ABS 7035	For B 0808.., B 1008.., B 1408.., B 1808..	Light grey
96930103	B SC HB 08 ABS 1023	For B 0808.., B 1008.., B 1408.., B 1808..	Traffic yellow



Wall brackets

96510005	B WL 7035	For B 08... - B 26...	Light grey
96510004	B WL 7024	For B 08... - B 26...	Graphite grey




Mounting panels, laminated paper, 2 mm

96602100 B M 1008 For B 1008..



Front panels, 2 mm, natural-coloured anodised aluminium

96702100 B FP 1008 For B 1008.., front panel thickness 1.5 mm



Sets of screws

96300000 B SHR D (for optional screwing of enclosures B 0808 - 2617)

96600010 B M-SHR C (for fixing mounting panels B M 1008-2736)

96700000 B FP-SHR A (for fixing front panels)



Distance bolts

96756000 DIBLZ AK 30x7/IM3/56 ND = 2.4-2.6, for B...09 if a mounting plate is used

96758000 DIBLZ AK 30x5/IM3/58 ND = 2.4 - 2.6, for B...09



Blanking plugs to determine the hinge side

96410000 B VS 3000 Flame red

96410005 B VS 7035 Light grey

96410004 B VS 7024 Graphite grey



DIN rail acc. to DIN EN 60715 TH 15

22150701 TS 15 For EM/ET 207-210, EM/ET 225, B 1008..



DIN rail acc. to DIN EN 60715 G 32

22320701 TS 32 For EM/ET 208-210, EM/ET 225, B 1008..



DIN rail acc. to DIN EN 60715 TH 35

22350701 TS 35 For EM/ET 208-210, EM/ET 225, B 1008..



Pressure compensation membrane DAE

52011000 DAE-D11 Self-adhesive membrane ø 11 mm



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59006217 SHR Z KA30x8

SD = 3,0 / ND = 2,4-2,6 / KD = 6,0