


Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 5.08 mm, lettering field size: 4.98 x 10.5 mm, Number of individual labels: 10

Your advantages

- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 591786 |
| GTIN | 4017918591786 |
| Weight per Piece (excluding packing) | 1.340 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793

Technical data

General


| | |
|--|--------------------------------|
| Note | Can be labeled with CMS |
| Color | white |
| Type | high |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |
| Marking mounting type | snap into tall marker groove |

Standards and Regulations

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2 |

Drawings

Schematic diagram



Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141137 |
| eCl@ss 11.0 | 27281101 |
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |
| ETIM 6.0 | EC000761 |
| ETIM 7.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131505 |
| UNSPSC 18.0 | 39131505 |
| UNSPSC 19.0 | 39131505 |
| UNSPSC 20.0 | 39131505 |
| UNSPSC 21.0 | 39131505 |

Accessories

Accessories

Magazine

Magazine insert - CMS-P1-M/ZB - 5144699



Plastic magazines for CMS-P1-PLOTTER and PLOTMARK. For accommodating 22 zack marker strips