

TY200-40X



CBL TIE 40LB 8IN UV BLACK NYL



General Information

Extended Product Type	TY200-40X
Product ID	7TAG054360R0228
EAN	5414363061311
Catalog Description	CBL TIE 40LB 8IN UV BLACK NYL
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 204.72mm (8.06 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Bulk Pack

Ordering

EAN	5414363061311
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.002 lb .907 g
--------------------	-------------------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	1.25 in 32 mm
Package Level 1 Height	14 in 356 mm
Package Level 1 Depth / Length	18 in 457 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13 in 330 mm
Package Level 2 Height	13.7 in 348 mm
Package Level 2 Depth / Length	14.5 in 368 mm

Additional Information

Brand / Label	Ty-Fast
---------------	---------

Bundle Diameter	0.06 to 1.97 in 1.6 to 50 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6 Weather Resistant
Product Name	NYLON CABLE TIE
Product Type	Intermediate
Special Functions	The integrally formed nylon pawl combines low insertion and high locking strength.
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm
UPC	786210283357

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY200-40X
Instructions and Manuals	TY200-40X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

