

## LED Floodlights



VT-10-G

### HIGHLIGHTS :

WATTS



10

EQ. WATTS



100

LUMINOUS



800

BEAM ANGLE



100

### PRODUCT FEATURES

Item No	:	VT-10-G
SKU Code	:	431
Watts	:	10
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	800
Color Temperature	:	4000K
Beam Angle	:	100
PF	:	>0.9
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP65
Body type	:	Die casting Aluminium
Dimmable	:	-
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +50°C
EAN code	:	3800157630870
Unit size	:	115x108x26mm
Packing details	:	20.00