


Self-aligning ball bearings, cylindrical and tapered bore, cylindrical bore, seal on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
17	40	16	8,84	2,2	0,12	-	12000	0,089	2203 E-2RS1TN9



Calculation factors

- $e = 0,31$
- $Y_1 = 2$
- $Y_2 = 3,1$
- $Y_0 = 2,2$