

SPECIAL ELECTRONIC PLIERS EUROline-Conductive

CUTTING PLIERS



No.	Length		Finish	cutting capacity mm Ø			Weight g
	mm	inches		Medium hard wire	Hard wire	Piano-wire	

Carbide mini side cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
only for tough nickel and electrode wires

3-661-15	120	4 3/4	with side face very slim rounded head	1.2	1.0	0.6	70
3-663-15	120	4 3/4	with side face very slim pointed head with special flat cutting edge	0.6	0.5	-	65



3-661-15




3-663-15

Carbide oblique top cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
cutting plane 29° angular, for horizontal and vertical use,
only for tough nickel and electrode wires

3-667-15	115	4 1/2	without side face	0.6	0.5	0.3	65
----------	-----	-------	-------------------	-----	-----	-----	----



3-667-15



3-665-15

Glas fibre mini side cutters EUROline-Conductive

for continuous heavy work, **with inserted carbide cutting edges**,
with special side face, **for cutting glass fibre only**, max. Ø 2.0 mm

3-665-15	120	4 3/4	very slim rounded head				70
----------	-----	-------	------------------------	--	--	--	----

ROUND, FLAT, SNIPE NOSE PLIERS

No.	Length		Finish	Weight g
	mm	inches		

Round nose pliers EUROline-Conductive

extremely slim

3-681-15	130	5 1/8	short plain jaws	60
----------	-----	-------	------------------	----



3-682-15



3-681-15

Flat nose pliers EUROline-Conductive

extremely slim

3-682-15	130	5 1/8	short plain jaws	70
----------	-----	-------	------------------	----

3-688-15	130	5 1/8	short, ultra slim plain jaws	60
----------	-----	-------	-------------------------------------	----



3-683-15



3-688-15

Snipe nose pliers EUROline-Conductive

extremely slim

3-683-15	130	5 1/8	short plain jaws	70
----------	-----	-------	------------------	----

3-685-15	140	5 1/2	long plain jaws	70
----------	-----	-------	-----------------	----

3-686-15	140	5 1/2	long serrated jaws	70
----------	-----	-------	--------------------	----

3-687-15	130	5 1/8	short plain jaws, ultra slim pointed for precise handling of tiny components	70
----------	-----	-------	--	----



3-687-15



3-685-15