


Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
15	35	11	8,06	3,75	0,16	43000	22000	0,045	6202-2Z *



Calculation factors

k_r 0,025

f_0 13