



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon6T, UL94V-0
PIN Phosphoric bronze Tin-plated
Solder tads Phosphoric bronze Tin-plated



Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-CB1.25-2AWT-02	1.25	7.65
3	HC-CB1.25-3AWT-02	2.50	8.90
4	HC-CB1.25-4AWT-02	3.75	10.15
5	HC-CB1.25-5AWT-02	5.00	11.40
6	HC-CB1.25-6AWT-02	6.25	12.65
7	HC-CB1.25-7AWT-02	7.50	13.90
8	HC-CB1.25-8AWT-02	8.75	15.15
9	HC-CB1.25-9AWT-02	10.00	16.40
10	HC-CB1.25-10AWT-02	11.25	17.65
11	HC-CB1.25-11AWT-02	12.50	18.90
12	HC-CB1.25-12AWT-02	13.75	20.15

1.25超薄-卧贴, 我司有两款产品, 通过的电流、电压都是一致的



GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
DIM TOL		审核 CHECK		产品名称 TITLE		版本 REV.	A
X.X	±0.20	批准 APPROVAL		1.25超薄 卧贴			
X.XX	±0.15	比例 SCALE		产品料号 PART NO.		单位 UNITS	mm
X.XXX	±0.10	投影 Projection		HC-CB1.25-NAWT-02		页次 SHEET	1/1
Angle	±2.0°			材料 MATERIAL			

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE
1	初版发行	