


KEMET Part Number: ALT22A102AB100 Not for New Design
(A663CG102M100A)

ALT22, Aluminum Electrolytic, 1,000 uF, 20%, 100 VDC, -40/+85°C



General Information	
Supplier:	KEMET
Series:	ALT22
Dielectric:	Aluminum Electrolytic
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing

Dimensions	
D	25mm +/-1mm
L	45mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications	
Weight:	39 g
Slewing:	Yes
Packaging:	Bulk, Bag

Specifications	
Capacitance:	1,000 uF
Capacitance Tolerance:	20%
Voltage DC:	100 VDC, 115 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	12000 Hrs
Leakage Current:	600 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.