
Mallory	Mallory Sonalert Products Inc.	Part #	ASI09N27M-05Q
Sales	Outline Drawing	Revision	E

May not be suitable for all Medical and Aerospace applications. Contact Mallory Sonalert to discuss your application.

Contact Manory Sonaicrt to discuss your application.				
Oscillation Frequency (Hz)	2700 ± 300			
Operating Voltage (Vdc)	3.0 ~ 7.0			
Rated Voltage (Vdc)	5.0			
Current Consumption Max. (mA)	30 at Rated Voltage			
Sound Pressure Level (dB/min)	80 at 10cm at Rated Voltage			
Tone/Pulse Rate	Constant			
Operating Temperature (°C)	-20 ~ +70			
Storage Temperature (°C)	-30 ~ +80			
Lead Pin	SMD			
Housing	PPS Plastic Resin (Black)			
Condition by reflow soldering (°C)	250 ± 5 / within 5 sec			
Condition by hand soldering (°C)	350 ± 20 / within 5 sec			
Weight (Grams)	2.5			
Options	For other options contact factory			

Dimensions: (units: mm) ROHS Compliant



Packaging:

Parts are supplied on Cut-Tape.

Units come with wash label and are appropriate for aqueous wash.