


Product number: 037172



Description:

Brand: Legrand  
 Series: Viking3 klemmenstroken  
 Product Class: Verbindingsrijgklem  
 Price (per 1 st ):  
 Start Date: 1-1-2014  
 Discount Group: L5  
 Net Weight (kg): 0,021

Features

Connectable conductor cross section fine-strand without cable (mm <sup>2</sup> ):	0.25 - 6	Connectable conductor cross section solid-core (mm <sup>2</sup> ):	0.5 - 10
Connectable conductor cross section multi-wired (mm <sup>2</sup> ):	0.5 - 2.5	Rated voltage (V):	500
Type of electrical connection 1:	Screw connection	Type of electrical connection 2:	Screw connection
Connection position:	Sideways	Number of levels:	1
Number of clamp positions per level:	2	Mounting method:	DIN rail (top hat rail) 35 mm
Material insulation body:	Other	Operation temperature (°C):	-5 - 40
Inflammability class of insulation material acc. with UL94:	V2	Width/grid dimension (mm):	52.2
Height at lowest possible mounting height (mm):	46.4	Explosion-tested version 'Ex e':	Yes
Closing plate required:	Yes	Colour:	Green-yellow
Internally connected stages:	No	Height (mm):	46.4
Material:	Plastic	Surface treatment:	Polyamide

Prices are valid for the Dutch market. All prices are gross, excluding VAT. Technical and / or price changes and mistakes are possible.