

Specifications:

Model	ST-60
Power consumption	60W
Input voltage	110VAC/220VAC $\pm 10\%$ 50Hz/60Hz
Heater voltage	26VAC
Heater	High performance dual-core ceramic heater
Display method	LCD
Temperature range	150°C~450°C/302°F~842°F
Temperature offset range	$\pm 50^{\circ}\text{C}$ ($\pm 90^{\circ}\text{F}$)
Temperature stability	$\pm 2^{\circ}\text{C}$ at idle temperature
Tip to ground resistance	$< 2\Omega$
Tip to ground potential	$< 2\text{mV}$
Auto-sleep	0~120 minutes
Auto turn off the heating	0~120 minutes
Temperature accuracy	$\pm 15^{\circ}\text{C}$