

Спецификация ST-80

Model	ST-80
Power consumption	80W
Input voltage	110VAC/220VAC ±10% 50Hz/60Hz
Output voltage	28VAC
Display method	LCD
Temperature range	150°C~480°C/302°F~896°F
Temperature offset range	±50°C (±90°F)
Temperature stability	±2°C at idle temperature
Tip to ground resistance	<2Ω
Tip to ground potential	<2mV
Auto-sleep	0~120 minutes
Auto turn off the heating	0~120 minutes