





REV.	CNN	CNN DESCRIPTION	Date	Check in
02			02/02/2010	Shaun Barron



### ELECTRICAL SPECIFICATION

RATED VOLTAGE	250V
RATED CURRENT	6A @40°C
FREQUENCY	50/60Hz
TEMPERATURE RANGE	-25° TO 85°C
EARTH LEAKAGE CURRENT	0.47mA @230V 50Hz
TEST VOLTAGE	2.0kV dc
TERMINATIONS:	
EN60320 (IEC320) APPLIANCE INLET	
EN60320 (IEC320) APPLIANCE OUTLET	
METAL OXIDE VARISTOR	L - N 275V

RoHS  
2002/95/EC  
Compliant

Tel No.+44(0)1724273200 Website www.dem-uk.com



**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ALPHA 3 MANUFACTURING.  
ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF ALPHA 3 MANUFACTURING IS PROHIBITED.

DEM Manufacturing, Deltron Emcon House  
Hargreaves Way, Sawcliffe Ind. Park,  
Scunthorpe, North Lincolnshire, DN15 8RF, UK

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN MILLIMETRES  
LINEAR TOLERANCE:  
**NO DECIMAL PLACES ±0.5mm**  
**1 DECIMAL PLACE ±0.25mm**  
**2 DECIMAL PLACES ±0.125mm**  
ANGULAR TOLERANCE: ±1°

FINISH	.	DEBURR AND BREAK SHARP EDGES	DRAWN BY SW	TITLE GENERAL SPECIFICATION 250V 6A 50/60Hz PORTABLE MAINS FILTER
			APPROVED BY BS	
			THIRD ANGLE PROJECTION	DRAWING NO. PMF6
			SHEET 1 OF 1	ISSUE 02
			SCALE 2:3	Release
MATERIAL	.		A3	
		IF IN DOUBT ASK DO NOT SCALE DRAWING		