



Click [here](#) for the 3D model.

Dimensions

D	25mm MAX
T	21mm MAX
H	25mm MAX
LL	3.5mm +/-1mm
S	6.5mm NOM
S1	17.6mm NOM
Wire Size	0.8mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	360
Component Weight	15 g

General Information

Series	SC-D-J/JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	30 uH
Current	5 A
Temperature Range	-25/+105°C
DC Resistance	20 mOhms