



Click [here](#) for the 3D model.

Dimensions

D	17mm MAX
T	14mm MAX
LL	8mm +/-1.5mm
S	6mm NOM
S1	10mm NOM
Wire Size	0.65mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	3000
Component Weight	3.8 g

General Information

Series	SC-G/GS
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	0.105 mH (1 kHz)
Current	6 A
Temperature Range	-25/+105°C
DC Resistance	10 mOhms