

Hot Swappable, Dual I²C Isolators

Data Sheet

ADuM1250/ADuM1251

FEATURES

Bidirectional I²C communication
Open-drain interfaces
Suitable for hot swap applications
30 mA current sink capability
1000 kHz operation
3.0 V to 5.5 V supply/logic levels
8-lead, RoHS-compliant SOIC package
High temperature operation: 125°C
Qualified for automotive applications
Safety and regulatory approvals

UL recognition
2500 V rms for 1 minute per UL 1577
CSA Component Acceptance Notice #5A
VDE certificate of conformity
DIN V VDE V 0884-10 (VDE V 0884-10):2006-12
V_{IORM} = 560 V peak

APPLICATIONS

Isolated I²C, SMBus, or PMBus interfaces Multilevel I²C interfaces Power supplies Networking Power-over-Ethernet Hybrid electric vehicle battery management

GENERAL DESCRIPTION

The ADuM1250/ADuM1251¹ are hot swappable digital isolators with nonlatching, bidirectional communication channels that are compatible with I^2C interfaces. This eliminates the need for splitting I^2C signals into separate transmit and receive signals for use with standalone optocouplers.

The ADuM1250 provides two bidirectional channels, supporting a complete isolated I²C interface. The ADuM1251 provides one bidirectional channel and one unidirectional channel for applications where a bidirectional clock is not required.

FUNCTIONAL BLOCK DIAGRAMS




Figure 1. ADuM1250




Figure 2. ADuM1251

Both the ADuM1250 and the ADuM1251 contain hot swap circuitry to prevent glitching data when an unpowered card is inserted onto an active bus.

These isolators are based on the *i*Coupler* chip scale transformer technology from Analog Devices, Inc. *i*Coupler is a magnetic isolation technology with functional, performance, size, and power consumption advantages as compared to optocouplers. With the ADuM1250/ADuM1251, *i*Coupler channels can be integrated with semiconductor circuitry, which enables a complete isolated I²C interface to be implemented in a small form factor.

¹ Protected by U.S. Patents 5,952,849; 6,873,065; and 7,075,329.

TABLE OF CONTENTS

Features	1
Applications	1
Functional Block Diagrams	1
General Description	1
Revision History	2
Specifications	3
Electrical Characteristics	3
Package Characteristics	5
Regulatory Information	5
Insulation and Safety-Related Specifications	5
DIN V VDE V 0884-10 (VDE V 0884-10) Insulation	
Characteristics	6
Recommended Operating Conditions	6
REVISION HISTORY	
9/12—Rev. E to Rev. F	
Created Hyperlink for Safety and Regulatory Approvals	
Entry in Features Section	
Changes to Ordering Guide	12
12/11—Rev. D to Rev. E	
Change to Ordering Guide	
Changes to Automotive Products Section	12
7/11—Rev. C to Rev. D	
Change to Typical Application Diagram Section	11
5/10—Rev. B to Rev. C	
Changes to Features Section and Applications Section	1
Changed $V_{DD1} = 5 \text{ V}$, and $V_{DD2} = 5 \text{ V}$ to $V_{DD1} = 3.3 \text{ V}$ or 5 V ,	
and V_{DD2} = 3.3 V or 5 V Changed V_{DD1} = 5 V, and V_{DD2} = 5 V to V_{DD1} = 3.3 V or 5 V,	3
and $V_{DD2} = 3.3 \text{ V or 5 V}$	4
Changes to Typical Application Diagram Section	7
and Figure 9	
Changes to Ordering Guide	
Added Automotive Products Section	12

Absolute Maximum Ratings	/
ESD Caution	7
Pin Configuration and Function Descriptions	8
Test Conditions	9
Applications Information	10
Functional Description	10
Startup	10
Typical Application Diagram	10
Magnetic Field Immunity	11
Outline Dimensions	12
Ordering Guide	12
Automotive Products	12

12/09—Rev. A to Rev. B

Changes to Operating Temperature (T _A) Parameter,	1able /
Changes to Ambient Operating Temperature (TA) Pa	arameter,
Table 8	7
Changes to Ordering Guide	12
6/07—Rev. 0 to Rev. A	
Updated VDE Certification Throughout	1
Changes to Features and Note 1	1
Changes to Table 4 and Table 5	5
Changes to Table 6	6
Undated Outline Dimensions	12

Changes to Features Section1

10/06—Revision 0: Initial Version

SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

DC Specifications¹

All minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted. All typical specifications are at T_A = 25°C, V_{DD1} = 3.3 V or 5 V, and V_{DD2} = 3.3 V or 5 V, unless otherwise noted.

Table 1.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
ADuM1250						
Input Supply Current, Side 1, 5 V	I _{DD1}		2.8	5.0	mA	$V_{DD1} = 5 V$
Input Supply Current, Side 2, 5 V	I _{DD2}		2.7	5.0	mA	$V_{DD2} = 5 V$
Input Supply Current, Side 1, 3.3 V	I _{DD1}		1.9	3.0	mA	$V_{DD1} = 3.3 \text{ V}$
Input Supply Current, Side 2, 3.3 V	I _{DD2}		1.7	3.0	mA	$V_{DD2} = 3.3 \text{ V}$
ADuM1251						
Input Supply Current, Side 1, 5 V	I _{DD1}		2.8	6.0	mA	$V_{DD1} = 5 V$
Input Supply Current, Side 2, 5 V	I _{DD2}		2.5	4.7	mA	$V_{DD2} = 5 V$
Input Supply Current, Side 1, 3.3 V	I _{DD1}		1.8	3.0	mA	$V_{DD1} = 3.3 \text{ V}$
Input Supply Current, Side 2, 3.3 V	I _{DD2}		1.6	2.8	mA	$V_{DD2} = 3.3 \text{ V}$
LEAKAGE CURRENTS	I _{SDA1} , I _{SDA2} ,		0.01	10	μΑ	$V_{SDA1} = V_{DD1}, V_{SDA2} = V_{DD2},$
	I _{SCL1} , I _{SCL2}					$V_{SCL1} = V_{DD1}, V_{SCL2} = V_{DD2}$
SIDE 1 LOGIC LEVELS						
Logic Input Threshold ²	V_{SDA1T}, V_{SCL1T}	500		700	mV	
Logic Low Output Voltages	V_{SDA1OL}, V_{SCL1OL}	600		900	mV	$I_{SDA1} = I_{SCL1} = 3.0 \text{ mA}$
		600		850	mV	$I_{SDA1} = I_{SCL1} = 0.5 \text{ mA}$
Input/Output Logic Low Level Difference ³	ΔV_{SDA1} , ΔV_{SCL1}	50			mV	
SIDE 2 LOGIC LEVELS						
Logic Low Input Voltage	V_{SDA2IL}, V_{SCL2IL}			$0.3V_{DD2}$	V	
Logic High Input Voltage	V_{SDA2IH}, V_{SCL2IH}	$0.7\mathrm{V}_{\mathrm{DD2}}$			V	
Logic Low Output Voltage	V _{SDA2OL} , V _{SCL2OL}			400	mV	$I_{SDA2} = I_{SCL2} = 30 \text{ mA}$

 $^{^1}$ All voltages are relative to their respective ground. 2 V $_{IL}$ < 0.5 V, V $_{IH}$ > 0.7 V.

 $^{^{3}}$ $\Delta V_{51} = V_{5101} - V_{517}$. This is the minimum difference between the output logic low level and the input logic threshold within a given component. This ensures that there is no possibility of the part latching up the bus to which it is connected.

ADuM1250/ADuM1251 **Data Sheet**

AC Specifications¹

All minimum/maximum specifications apply over the entire recommended operating range, unless otherwise noted. All typical specifications are at $T_A = 25$ °C, $V_{DD1} = 3.3$ V or 5 V, and $V_{DD2} = 3.3$ V or 5 V, unless otherwise noted. Refer to Figure 5.

Table 2.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
MAXIMUM FREQUENCY		1000			kHz	
OUTPUT FALL TIME						
5 V Operation						$4.5 \text{ V} \le \text{V}_{\text{DD1}}, \text{V}_{\text{DD2}} \le 5.5 \text{ V}, \text{C}_{\text{L1}} = 40 \text{ pF},$ $\text{R1} = 1.6 \text{ kΩ}, \text{C}_{\text{L2}} = 400 \text{ pF}, \text{R2} = 180 \Omega$
Side 1 Output (0.9 V _{DD1} to 0.9 V)	t _{f1}	13	26	120	ns	
Side 2 Output (0.9 V_{DD2} to 0.1 V_{DD2})	t _{f2}	32	52	120	ns	
3 V Operation						$3.0 \text{ V} \le \text{V}_{\text{DD1}}, \text{V}_{\text{DD2}} \le 3.6 \text{ V}, \text{C}_{\text{L1}} = 40 \text{ pF},$ $\text{R1} = 1.0 \text{ k}\Omega, \text{C}_{\text{L2}} = 400 \text{ pF}, \text{R2} = 120 \Omega$
Side 1 Output (0.9 V _{DD1} to 0.9 V)	t _{f1}	13	32	120	ns	
Side 2 Output (0.9 V_{DD2} to 0.1 V_{DD2})	t _{f2}	32	61	120	ns	
PROPAGATION DELAY						
5 V Operation						4.5 \leq V _{DD1} , V _{DD2} \leq 5.5 V, C _{L1} = C _{L2} = 0 pF, R1 = 1.6 k Ω , R2 = 180 Ω
Side 1-to-Side 2, Rising Edge ²	t _{PLH12}		95	130	ns	
Side 1-to-Side 2, Falling Edge ³	t _{PHL12}		162	275	ns	
Side 2-to-Side 1, Rising Edge ⁴	t _{PLH21}		31	70	ns	
Side 2-to-Side 1, Falling Edge⁵	t _{PHL21}		85	155	ns	
3 V Operation						$3.0 \text{ V} \le \text{V}_{\text{DD1}}, \text{V}_{\text{DD2}} \le 3.6 \text{ V}, \text{C}_{\text{L1}} = \text{C}_{\text{L2}} = 0 \text{ pF},$ $\text{R1} = 1.0 \text{ k}\Omega, \text{R2} = 120 \Omega$
Side 1-to-Side 2, Rising Edge ²	t _{PLH12}		82	125	ns	
Side 1-to-Side 2, Falling Edge ³	t _{PHL12}		196	340	ns	
Side 2-to-Side 1, Rising Edge ⁴	t _{PLH21}		32	75	ns	
Side 2-to-Side 1, Falling Edge⁵	t _{PHL21}		110	210	ns	
PULSE WIDTH DISTORTION						
5 V Operation						4.5 V \leq V _{DD1} , V _{DD2} \leq 5.5 V, C _{L1} = C _{L2} = 0 pF, R1 = 1.6 k Ω , R2 = 180 Ω
Side 1-to-Side 2, $ t_{PLH12} - t_{PHL12} $	PWD ₁₂		67	145	ns	
Side 2-to-Side 1, $ \mathbf{t}_{PLH21} - \mathbf{t}_{PHL21} $	PWD ₂₁		54	85	ns	
3 V Operation						$3.0 \text{ V} \le \text{V}_{\text{DD1}}, \text{V}_{\text{DD2}} \le 3.6 \text{ V}, \text{C}_{\text{L1}} = \text{C}_{\text{L2}} = 0 \text{ pF},$ $\text{R1} = 1.0 \text{ k}\Omega, \text{R2} = 120 \Omega$
Side 1-to-Side 2, $ t_{PLH12} - t_{PHL12} $	PWD ₁₂		114	215	ns	
Side 2-to-Side 1, $\left \mathbf{t}_{\text{PLH21}} - \mathbf{t}_{\text{PHL21}}\right $	PWD ₂₁		77	135	ns	
COMMON-MODE TRANSIENT IMMUNITY ⁶	CM _H , CM _L	25	35		kV/μs	

¹ All voltages are relative to their respective ground.

² t_{PLH12} propagation delay is measured from the Side 1 input logic threshold to an output value of 0.7 V_{DD2}.

³ t_{PH12} propagation delay is measured from the Side 1 input logic threshold to an output value of 0.4 V.

⁴ t_{PLH21} propagation delay is measured from the Side 2 input logic threshold to an output value of 0.7 V_{DD1}.

 $^{^{5}}$ $t_{PHI,21}$ propagation delay is measured from the Side 2 input logic threshold to an output value of 0.9 V.

 $^{^6}$ CM_H is the maximum common-mode voltage slew rate that can be sustained while maintaining V_o > 0.8 V_{DD2}. CM_L is the maximum common-mode voltage slew rate that can be sustained while maintaining V_o < 0.8 V. The common-mode voltage slew rates apply to both rising and falling common-mode voltage edges. The transient magnitude is the range over which the common mode is slewed.

PACKAGE CHARACTERISTICS

Table 3.

Parameter	Symbol	Min	Тур	Max	Unit	Test Conditions/Comments
Resistance (Input to Output) ¹	R _{I-O}		10 ¹²		Ω	
Capacitance (Input to Output) ¹	C _{I-O}		1.0		рF	f = 1 MHz
Input Capacitance	Cı		4.0		рF	
IC Junction-to-Case Thermal Resistance, Side 1	θ_{JCI}		46		°C/W	Thermocouple located at center of package underside
IC Junction-to-Case Thermal Resistance, Side 2	θ_{JCO}		41		°C/W	

¹ The device is considered a 2-terminal device; Pin 1 through Pin 4 are shorted together, and Pin 5 through Pin 8 are shorted together.

REGULATORY INFORMATION

The ADuM1250/ADuM1251 have been approved by the organizations listed in Table 4.

Table 4.

UL	CSA	VDE
Recognized under 1577 Component Recognition Program ¹	Approved under CSA Component Acceptance Notice #5A	Certified according to DIN V VDE V 0884-10 (VDE V 0884-10):2006-12 ²
Single/basic 2500 V rms isolation voltage	Reinforced insulation per CSA 60950-1-03 and IEC 60950-1, 125 V rms (177 V peak) maximum working voltage Basic insulation per CSA 60950-1-03 and IEC 60950-1, 400 V rms (566 V peak) maximum working voltage	Reinforced insulation, 560 V peak
File E214100	File 205078	File 2471900-4880-0001

¹ In accordance with UL 1577, each ADuM1250/ADuM1251 is proof tested by applying an insulation test voltage ≥ 3000 V rms for 1 sec (current leakage detection

INSULATION AND SAFETY-RELATED SPECIFICATIONS

Table 5.

Parameter	Symbol	Value	Unit	Test Conditions/Comments
Rated Dielectric Insulation Voltage		2500	V rms	1-minute duration
Minimum External Air Gap (Clearance)	L(I01)	4.90 min	mm	Measured from input terminals to output terminals, shortest distance through air
Minimum External Tracking (Creepage)	L(102)	4.01 min	mm	Measured from input terminals to output terminals, shortest distance path along body
Minimum Internal Gap (Internal Clearance)		0.017 min	mm	Insulation distance through insulation
Tracking Resistance (Comparative Tracking Index)	CTI	>175	V	DIN IEC 112/VDE 0303 Part 1
Isolation Group		Illa		Material Group (DIN VDE 0110, 1/89, Table 1)
Maximum Working Voltage Compatible with 50 Years Service Life	V _{IORM}	565	V peak	Continuous peak voltage across the isolation barrier

² In accordance with DIN V VDE V 0884-10, each ADuM1250/ADuM1251 is proof tested by applying an insulation test voltage ≥ 1050 V peak for 1 sec (partial discharge detection limit = 5 pC). The asterisk (*) marking branded on the component designates DIN V VDE V 0884-10 approval.

ADuM1250/ADuM1251 Data Sheet

DIN V VDE V 0884-10 (VDE V 0884-10) INSULATION CHARACTERISTICS

This isolator is suitable for reinforced isolation only within the safety limit data. Maintenance of the safety data is ensured by protective circuits. The asterisk (*) marking on the package denotes DIN V VDE V 0884-10 approval for a 560 V peak working voltage.

Table 6.

Description	Test Conditions/Comments	Symbol	Characteristic	Unit
Installation Classification per DIN VDE 0110				
For Rated Mains Voltage ≤ 150 V rms			I to IV	
For Rated Mains Voltage ≤ 300 V rms			I to III	
For Rated Mains Voltage ≤ 400 V rms			l to II	
Climatic Classification			40/105/21	
Pollution Degree per DIN VDE 0110, Table 1			2	
Maximum Working Insulation Voltage		V_{IORM}	560	V peak
Input-to-Output Test Voltage, Method B1	$V_{IORM} \times 1.875 = V_{PR}$, 100% production test, $t_m = 1$ sec, partial discharge < 5 pC	V_{PR}	1050	V peak
Input-to-Output Test Voltage, Method A	$V_{IORM} \times 1.6 = V_{PR}$, $t_m = 60$ sec, partial discharge < 5 pC	V_{PR}		
After Environmental Tests Subgroup 1			896	V peak
After Input and/or Safety Tests Subgroup 2 and Subgroup 3	$V_{IORM} \times 1.2 = V_{PR}$, $t_m = 60$ sec, partial discharge < 5 pC		672	V peak
Highest Allowable Overvoltage	Transient overvoltage, t _{TR} = 10 sec	V_{TR}	4000	V peak
Safety-Limiting Values	Maximum value allowed in the event of a failure (see Figure 3)			
Case Temperature		T _s	150	°C
$V_{DD1} + V_{DD2}$ Current		I _{TMAX}	212	mA
Insulation Resistance at T _s	$V_{IO} = 500 \text{ V}$	R_s	>109	Ω




Figure 3. Thermal Derating Curve, Dependence of Safety-Limiting Values on Case Temperature, per DIN V VDE V 0884-10

RECOMMENDED OPERATING CONDITIONS

Table 7.

Table 7.	
Parameter	Rating
Operating Temperature (T _A)	
A Grade	-40°C to +105°C
S Grade	-40°C to +125°C
Supply Voltages (V _{DD1} , V _{DD2}) ¹	3.0 V to 5.5 V
Input/Output Signal Voltage	5.5 V
$(V_{SDA1}, V_{SCL1}, V_{SDA2}, V_{SCL2})$	
Capacitive Load	
Side 1 (C _{L1})	40 pF
Side 2 (C _{L2})	400 pF
Static Output Loading	
Side 1 (I _{SDA1} , I _{SCL1})	0.5 mA to 3 mA
Side 2 (I _{SDA2} , I _{SCL2})	0.5 mA to 30 mA

¹ All voltages are relative to their respective ground. See the Magnetic Field Immunity section for information about immunity to external magnetic fields.

Data Sheet ADuM1250/ADuM1251

ABSOLUTE MAXIMUM RATINGS

Ambient temperature = 25°C, unless otherwise noted.

Table 8.

Parameter	Rating
Storage Temperature (T _{ST})	−55°C to +150°C
Ambient Operating Temperature (T_A)	
A Grade	-40°C to +105°C
S Grade	−40°C to +125°C
Supply Voltages (V _{DD1} , V _{DD2}) ¹	−0.5 V to +7.0 V
Input/Output Voltage,	
Side 1 (V _{SDA1} , V _{SCL1}) ¹	$-0.5 \mathrm{V}$ to $\mathrm{V}_{\mathrm{DD1}} + 0.5 \mathrm{V}$
Side 2 (V _{SDA2} , V _{SCL2}) ¹	$-0.5 \text{ V to V}_{DD2} + 0.5 \text{ V}$
Average Output Current per Pin ²	
Side 1 (I _{O1})	±18 mA
Side 2 (I _{O2})	±100 mA
Common-Mode Transients ³	−100 kV/µs to +100 kV/µs

¹ All voltages are relative to their respective ground.

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational section of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ESD CAUTION



ESD (electrostatic discharge) sensitive device. Charged devices and circuit boards can discharge without detection. Although this product features patented or proprietary protection circuitry, damage may occur on devices subjected to high energy ESD. Therefore, proper ESD precautions should be taken to avoid performance degradation or loss of functionality.

² See Figure 3 for maximum rated current values for various temperatures.

³ Refers to common-mode transients across the insulation barrier. Common-mode transients exceeding the absolute maximum rating may cause latch-up or permanent damage.

ADuM1250/ADuM1251 Data Sheet

PIN CONFIGURATION AND FUNCTION DESCRIPTIONS




Figure 4. ADuM1250/ADuM1251 Pin Configuration

Table 9. ADuM1250 Pin Function Descriptions

Pin No.	Mnemonic	Description	
1	V_{DD1}	Supply Voltage, 3.0 V to 5.5 V.	
2	SDA ₁	Data Input/Output, Side 1.	
3	SCL ₁	Clock Input/Output, Side 1.	
4	GND ₁	Ground 1. Ground reference for Isolator Side 1.	
5	GND ₂	Ground 2. Isolated ground reference for Isolator Side 2.	
6	SCL ₂	Clock Input/Output, Side 2.	
7	SDA ₂	Data Input/Output, Side 2.	
8	V_{DD2}	Supply Voltage, 3.0 V to 5.5 V.	

Table 10. ADuM1251 Pin Function Descriptions

Pin No.	Mnemonic	Description				
1	V_{DD1}	Supply Voltage, 3.0 V to 5.5 V.				
2	SDA ₁	Data Input/Output, Side 1.				
3	SCL ₁	Clock Input, Side 1.				
4	GND ₁	Ground 1. Ground reference for Isolator Side 1.				
5	GND ₂	Ground 2. Isolated ground reference for Isolator Side 2.				
6	SCL ₂	Clock Output, Side 2.				
7	SDA ₂	Data Input/Output, Side 2.				
8	V_{DD2}	Supply Voltage, 3.0 V to 5.5 V.				

Data Sheet ADuM1250/ADuM1251

TEST CONDITIONS




Figure 5. Timing Test Diagram

ADuM1250/ADuM1251 Data Sheet

APPLICATIONS INFORMATION FUNCTIONAL DESCRIPTION

The ADuM1250/ADuM1251 interface on each side to a bidirectional I²C signal. Internally, the I²C interface is split into two unidirectional channels communicating in opposing directions via a dedicated *i*Coupler isolation channel for each. One channel (the bottom channel of each channel pair shown in Figure 6) senses the voltage state of the Side 1 I²C pin and transmits its state to its respective Side 2 I²C pin.

Both the Side 1 and the Side 2 I^2C pins are designed to interface to an I^2C bus operating in the 3.0 V to 5.5 V range. A logic low on either pin causes the opposite pin to be pulled low enough to comply with the logic low threshold requirements of other I^2C devices on the bus. Avoidance of I^2C bus contention is ensured by an input low threshold at SDA_1 or SCL_1 guaranteed to be at least 50 mV less than the output low signal at the same pin. This prevents an output logic low at Side 1 being transmitted back to Side 2 and pulling down the I^2C bus.

Because the Side 2 logic levels/thresholds are standard I²C values, multiple ADuM1250/ADuM1251 devices connected to a bus by their Side 2 pins can communicate with each other and with other I²C-compatible devices. A distinction is made between I²C compatibility and I²C compliance. I²C compatibility refers to situations in which the logic levels of a component do not necessarily meet the requirements of the I²C specification but still allow the component to communicate with an I²C-compliant device. I²C compliance refers to situations in which the logic levels of a component meet the requirements of the I²C specification.

However, because the Side 1 pin has a modified output level/input threshold, this side of the ADuM1250/ADuM1251 can communicate only with devices that conform to the I²C standard. In other words, Side 2 of the ADuM1250/ADuM1251 is I²C-compliant, whereas Side 1 is only I²C-compatible.

The output logic low levels are independent of the $V_{\rm DD1}$ and $V_{\rm DD2}$ voltages. The input logic low threshold at Side 1 is also independent of $V_{\rm DD1}$. However, the input logic low threshold at Side 2 is designed to be at 0.3 $V_{\rm DD2}$, consistent with I²C requirements. The Side 1 and Side 2 pins have open-collector outputs whose high levels are set via pull-up resistors to their respective supply voltages.




Figure 6. ADuM1250 Block Diagram

STARTUP

Both the $V_{\rm DD1}$ and $V_{\rm DD2}$ supplies have an undervoltage lockout feature to prevent the signal channels from operating unless certain criteria are met. This feature prevents input logic low signals from pulling down the I^2C bus inadvertently during power-up/power-down.

For the signal channels to be enabled, the following two criteria must be met:

- Both supplies must be at least 2.5 V.
- At least 40 μs must elapse after both supplies exceed the internal startup threshold of 2.0 V.

Until both criteria are met for both supplies, the ADuM1250/ADuM1251 outputs are pulled high, ensuring a startup that avoids any disturbances on the bus. Figure 7 and Figure 8 illustrate the supply conditions for fast and slow input supply slew rates.




Figure 7. Start-Up Condition, Supply Slew Rate > 12.5 V/ms




Figure 8. Start-Up Condition, Supply Slew Rate < 12.5 V/ms

TYPICAL APPLICATION DIAGRAM

Figure 9 shows a typical application circuit including the pull-up resistors required for both Side 1 and Side 2 buses. Bypass capacitors with values from 0.01 μF to 0.1 μF are required between $V_{\rm DD1}$ and GND1 and between $V_{\rm DD2}$ and GND2. The 200 Ω resistor shown in Figure 9 is required for latch-up immunity if the ambient temperature can be between 105°C and 125°C.




Figure 9. Typical Isolated I²C Interface Using the ADuM1250

Data Sheet ADuM1250/ADuM1251

MAGNETIC FIELD IMMUNITY

The ADuM1250/ADuM1251 are extremely immune to external magnetic fields. The limitation on the magnetic field immunity of the ADuM1250/ADuM1251 is set by the condition in which induced voltage in the receiving coil of the transformer is sufficiently large to either falsely set or reset the decoder. The following analysis defines the conditions under which this may occur. The 3 V operating condition of the ADuM1250/ADuM1251 is examined because it represents the most susceptible mode of operation.

The pulses at the transformer output have an amplitude greater than $1.0~\rm V$. The decoder has a sensing threshold at approximately $0.5~\rm V$, thus establishing a $0.5~\rm V$ margin in which induced voltages can be tolerated. The voltage induced across the receiving coil is given by

$$V = (-d\beta/dt) \sum_{n} \pi r_n^2$$
; $n = 1, 2, ..., N$

where:

 β is the magnetic flux density (gauss). r_n is the radius of the nth turn in the receiving coil (cm). N is the total number of turns in the receiving coil.

Given the geometry of the receiving coil in the ADuM1250/ADuM1251 and an imposed requirement that the induced voltage be, at most, 50% of the 0.5 V margin at the decoder, a maximum allowable magnetic field is calculated as shown in Figure 10.




Figure 10. Maximum Allowable External Magnetic Flux Density

For example, at a magnetic field frequency of 1 MHz, the maximum allowable magnetic field of 0.2 kgauss induces a voltage of 0.25 V at the receiving coil. This voltage is approximately 50% of the sensing threshold and does not cause a faulty output transition. Similarly, if such an event occurs during a transmitted pulse (and is of the worst-case polarity), it reduces the received pulse from >1.0 V to 0.75 V—still well above the 0.5 V sensing threshold of the decoder.

The preceding magnetic flux density values correspond to specific current magnitudes at given distances away from the ADuM1250/ADuM1251 transformers. Figure 11 expresses these allowable current magnitudes as a function of frequency for selected distances. As shown in Figure 11, the ADuM1250/ADuM1251 are extremely immune and can be affected only by extremely large currents operated at high frequency very close to the component. For the 1 MHz example, a 0.5 kA current placed 5 mm away from the ADuM1250/ADuM1251 is required to affect the operation of the component.





Figure 11. Maximum Allowable Current for Various Current-to-ADuM1250/ADuM1251 Spacings

Note that at combinations of strong magnetic field and high frequency, any loops formed by PCB traces can induce error voltages sufficiently large to trigger the thresholds of succeeding circuitry. Exercise care in the layout of such traces to avoid this possibility.

OUTLINE DIMENSIONS



COMPLIANT TO JEDEC STANDARDS MS-012-AA
CONTROLLING DIMENSIONS ARE IN MILLIMETERS; INCH DIMENSIONS
(IN PARENTHESES) ARE ROUNDED-OFF MILLIMETER EQUIVALENTS FOR
REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN.

Figure 12. 8-Lead Standard Small Outline Package [SOIC_N] Narrow Body (R-8) Dimensions shown in millimeters and (inches)

ORDERING GUIDE

Model ^{1, 2}	Number of Inputs, V _{DD1} Side	Number of Inputs, V _{DD2} Side	Maximum Data Rate (Mbps)	Maximum Propagation Delay (ns)	Temperature Range	Package Description	Package Option
ADuM1250ARZ	2	2	1	150	-40°C to +105°C	8-Lead SOIC_N	R-8
ADuM1250ARZ-RL7	2	2	1	150	-40°C to +105°C	8-Lead SOIC_N	R-8
ADuM1250SRZ	2	2	1	150	-40°C to +125°C	8-Lead SOIC_N	R-8
ADuM1250SRZ-RL7	2	2	1	150	−40°C to +125°C	8-Lead SOIC_N	R-8
ADuM1250WSRZ	2	2	1	150	-40°C to +125°C	8-Lead SOIC_N	R-8
ADuM1250WSRZ-RL7	2	2	1	150	-40°C to +125°C	8-Lead SOIC_N	R-8
ADuM1251ARZ	2	1	1	150	-40°C to +105°C	8-Lead SOIC_N	R-8
ADuM1251ARZ-RL7	2	1	1	150	-40°C to +105°C	8-Lead SOIC_N	R-8
ADuM1251WARZ	2	2	1	150	−40°C to +125°C	8-Lead SOIC_N	R-8
ADuM1251WARZ-RL7	2	2	1	150	-40°C to +125°C	8-Lead SOIC_N	R-8

 $^{^{1}}$ Z = RoHS Compliant Part.

AUTOMOTIVE PRODUCTS

The ADuM1250W and ADuM1251W models are available with controlled manufacturing to support the quality and reliability requirements of automotive applications. Note that these automotive models may have specifications that differ from the commercial models; therefore, designers should review the Specifications section of this data sheet carefully. Only the automotive grade products shown are available for use in automotive applications. Contact your local Analog Devices account representative for specific product ordering information and to obtain the specific Automotive Reliability reports for these models.

 I^2C refers to a communications protocol originally developed by Philips Semiconductors (now NXP Semiconductors).



² W = Qualified for Automotive Applications.