


SC-10-D050

Aliases (UALSC10D050000)

KEMET, SC-D, AC Line Filters, Common Mode, 0.05 mH



Click [here](#) for the 3D model.

Dimensions

D	34mm MAX
H	23mm MAX
LL	15mm +/-2mm
S	22mm NOM
S1	21mm NOM
Wire Size	1.2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	200
Component Weight	34 g

General Information

Series	SC-D
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	50 uH
Current	10 A
Temperature Range	-25/+105°C
DC Resistance	16 mOhms