



Click [here](#) for the 3D model.

Dimensions

D	34mm MAX
T	22mm MAX
H	34mm MAX
LL	4mm +/-1.5mm
S	18mm NOM
S1	16mm NOM
Wire Size	1.2mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	180
Component Weight	34 g

General Information

Series	SC-D-J/JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Ni-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	50 uH
Current	10 A
Temperature Range	-25/+120°C
DC Resistance	16 mOhms