



Click [here](#) for the 3D model.

Dimensions

D	28mm MAX
H	19.5mm MAX
LL	5mm +/-2mm
S	20mm NOM
S1	14mm NOM
Wire Size	0.9mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	250
Component Weight	21.1g

General Information

Series	SC-JH
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 75 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	7 mH (10 kHz)
Current	6 A
Temperature Range	-25/+120°C
DC Resistance	70 mOhms