



Click [here](#) for the 3D model.

Dimensions

D	54.5mm MAX
T	54.5mm MAX
H	32.5mm MAX
LL	7mm +/-3mm
S	22mm NOM
S1	40mm NOM
Wire Size	1.8mm x 2P

Packaging Specifications

Packaging	Tray
Packaging Quantity	48
Component Weight	118.4 g

General Information

Series	SCR38
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 68 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Inductance	0.85 mH
Current	35 A
Temperature Range	-25/+120°C
DC Resistance	2.7 mOhms