



### General Information

Series	SU-9HD
Style	Through-Hole
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 70 K.

### Specifications

Voltage AC	250 VAC
Inductance	7.98 uH
Current	4 A
Temperature Range	-25/+120°C
DC Resistance	31.25 mOhms

Click [here](#) for the 3D model.

### Dimensions

L	17mm MAX
T	15.5mm MAX
H	12.5mm MAX
LL	3mm MAX
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.4mm

### Packaging Specifications

Packaging	Tray
Component Weight	2.9 g