



PIN OUT		
CN1	WIRE COLOR	CN2
1	WHITE	1
2	ORANGE	2
3	WHITE	3
6	GREEN	6
4	BLUE	4
5	WHITE	5
7	WHITE	7
8	BROWN	8
	SHELL	SHELL

② Tolerance

Length(meter)	Max-Δl	Min-Δl
0.5	+0.03	-0.025
1	+0.04	-0.035
2	+0.06	-0.06
3	+0.09	-0.09
5	+0.15	-0.15
7	+0.21	-0.21
10	+0.3	-0.3
15	+0.45	-0.45
20	+0.6	-0.6
30	+0.9	-0.9

① Order code: A-MC~~SS~~P60XXX : color Grey

order lengths in meter:  
0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30

① Order code: A-MC~~SS~~P60XXX/X

order lengths in meter:  
0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30

Electrical test:  
Open/Short/Intermittence: 100%

order color: (R)Red, (Y)Yellow, (G)Green, (B)Blue

NO.	NAME.	QTTY	DATE	NAME
③	Molding PVC	2	01.02.2016	Joanna
③	RJ45 CONN	2	01.11.2018	Amy
③	CABLE	1		

Scale	FREE	Customer-No.
TOLERANCE		ASSMANN WSW-No.
		A-MC <del>SS</del> P60XXX/X
		Drawing-No.
		ASS 7542 CA
		rev03
		Replace Sheet

**ROHS compliant**  
Unit: mm

1	2	3	4	5	6	7
1	2	3	4	5	6	7