

## AI 0,75- 8 GY-GB


Order No.: 1208979

The figure shows the version AI 0,75-8 GY

<http://catalog.phoenixcontact.net/phoenix/treeViewClick.do?UID=1208979>

Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: gray

### Commercial data

EAN	 4 046356 130394
sales group	B250
Pack	500 Pcs.
Customs tariff	85369010
Gross weight in pieces	0.000093 KG
Net weight per piece	0.000096 KG
Catalog page information	Page 448 (C-5-2013)

### Product notes

WEEE/RoHS-compliant since:  
03/09/2006

<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

### Technical data

#### Dimensions

Length (b)	14 mm
Maximum stripping length	11 mm
Sleeve length	8 mm
Inner dimension of the insulating collar (d)	3.4 mm
Ferrule diameter	1.3 mm
Insulating collar thickness	0.25 mm
Sleeve wall thickness	0.15 mm

**Ambient conditions**

Short-term temperature	120 °C
Max. permanent temperature	105 °C

**General**

Color	gray
Components	free from silicone and halogen
Inflammability class according to UL 94	HB
Material	E-CU

**Certificates / Approvals**



Certification cCSAus

Certifications applied for:

Certification Ex:

---

**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>



© 2014 Phoenix Contact  
Technical modifications reserved;