

End cover - D-ST 10

3036644

<https://www.phoenixcontact.com/us/products/3036644>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

End cover, length: 71.5 mm, width: 2.2 mm, height: 49.9 mm, color: gray



End cover - D-ST 10



3036644

<https://www.phoenixcontact.com/us/products/3036644>

Commercial Data

Item number	3036644
Packing unit	1 pc
Minimum order quantity	50 pc
Sales Key	B02
Product Key	BE2Z1X
Catalog Page	Page 243 (C-1-2019)
GTIN	4017918819682
Weight per Piece (including packing)	4.14 g
Weight per Piece (excluding packing)	4.12 g
Customs tariff number	85389099
Country of origin	DE

Technical Data

Product properties

Product type	End cover
--------------	-----------

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	2.2 mm
Height	49.9 mm
Length	71.5 mm

End cover - D-ST 10

3036644

<https://www.phoenixcontact.com/us/products/3036644>



Classifications

ECLASS

ECLASS-9.0	27141133
ECLASS-10.0.1	27141133
ECLASS-11.0	27141133

ETIM

ETIM 8.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

End cover - D-ST 10

3036644

<https://www.phoenixcontact.com/us/products/3036644>



Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com