


**PRODUCT NUMBER: 3912-0-01-15-00-00-08-0**



**DESCRIPTION**

Crimp Terminal Pin  
**Current Rating:**  
 Application Specific  
**Operating Temperature Range:**  
 -55/+125° C  
**Mounting Feature:**  
 Wire Mount  
**Wire Termination:**  
 Crimp 12-14 AWG  
**Tail Type:** Solder tail  
**Tail Diameter:** .094" (2,388mm)  
**Packaging:** 01 - Packaged in Bulk

<b>Shell Plating</b>	<b>Contact Plating</b>	<b>ROHS</b>
----------------------	------------------------	-------------

10 μ" Gold over Nickel



**STANDARD TOLERANCES ON PCB TERMINAL PINS & RECEPTACLES**

Diameters +/- .002"  
 Lengths +/- .005"  
 Angles +/- 2°

**STANDARD TOLERANCES ON SPRING-LOADED PINS**

Diameters +/- .002"  
 Lengths +/- .006"  
 Angles +/- 2°

**ADDITIONAL NOTES & SPECIFICATIONS**

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

© 2020 Mill-Max Mfg. Corp.  
 190 Pine Hollow Rd, Oyster Bay, NY 11771, USA  
 Phone: 516.922.6000