


vacuum suction cup ESV-30-BU

Part number: 191058

FESTO

Wearing part, easily replaceable



Data sheet

| Feature | Value |
|---|---|
| Suction cup height compensator | 8 mm |
| Min. workpiece radius | 80 mm |
| suction cup diameter | 30 mm |
| suction cup volume | 4.07 cm ³ |
| Position of connection | on top |
| Assembly position | Any |
| Suction cup shape | Round, bellows 1.5 conv |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Food-safe | See Supplementary material information |
| Ambient temperature | -20 ... 60 °C |
| Retention force at nominal operating pressure | 26.2 N |
| Product weight | 3.6 g |
| Colour | blue |
| Shore hardness | 60 +/- 5 |
| Materials note | Free of copper and PTFE Contains PWIS substances Conforms to RoHS |
| Material suction cup | PUR |