

Specification Sheet

Part Number: 211-60007



P-Clamps easily guide and locate wire and cables up to 1" in diameter. Designed with a radius edge to prevent chafing and cutting into insulation.

P-Clamp, 0.39" Wide, 0.55" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 100/pkg

Article Number 211-60007

Type H8P

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.

Short Description P-Clamp, 0.39" Wide, 0.55" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 100/pkg

Global Part Name H8P-PA66HS-BK

| | |
|--|------------|
| Fixation Method | screw-hole |
| Variant | Closed |
| Width W (Imperial) | 0.39 |
| Width W (Metric) | 10.0 |
| Bundle Diameter Max (Imperial) | 0.55 |
| Bundle Diameter Max (Metric) | 14.0 |
| Nominal Diameter (Imperial) | 0.5 |
| Nominal Diameter (Metric) | 14.0 |
| Wall Thickness WT (Imperial) | 0.059 |
| Wall Thickness WT (Metric) | 1.5 |
| Mounting Hole Diameter D (Imperial) | 0.17 |
| Mounting Hole Diameter D (Metric) | 4.2 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.17 |
| Mounting Hole Diameter D Max (Imperial) | 0.17 |
| Mounting Hole Diameter D Max (Metric) | 4.2 |
| Mounting Hole Centers (Imperial) | 0.59 |

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[211-60007](#)