


UL1007 22-24AWG 颜色：黑、紅 各一PCS。
 一端打（杜邦2.54）端子，另一端紅色錫100Ω電阻再打端子。

ELECTRICAL PROPERTIES:

1. 100% OPEN SHORT MIS-WIRE TEST
2. Conduction Resistance: 2 ohm max
3. Insulation resistance: 5Mega ohm MIN
4. Hi-Pot: 300V DC/10ms

Pin Assignment



NO.	DESCRIPTION	Q'TY	UNITS
5	TUBE: 4Φ 55mm X 2	2	pcs
4	Resistor:100Ω 1/4W ± 1%	1	PCS
3	HOUSING:DP 2.54mm-1PIN+2.54mm Terminals	1	SET
2	HOUSING:DP 2.54mm-2PIN+2.54mm Terminals	1	SET
1	WIRW:UL1007 24# RED & BLK	1	pcs

Tolerance: X. ± .X ± .XX ± .XXX ± X' ± .X' ±	Approved by: WXR	 SMOOTH CABLE & CONNECTOR CO., LTD.
	Checked by:	
	Drawn by: CDJ	
	Date: 2016.08.26	
Scale: Unit: None m/m	customer p/n: Resistor/2.54	Smooth p/n:
Specification Use Only	Description:	DWG NO:
		SHEET: 1/1
		REV: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Digilent:

240-116 410-349