

Series 801 Mighty Mouse Double-Start ACME Thread Right Angle PCB Receptacle

801-023 Ordering Information



Series 801



Right Angle PCB Receptacle

connectors offer military grade performance in a small, lightweight package. These connectors are rated for MIL-STD-810 Method 512 immersion. High temperature thermoplastic housing withstands soldering temperatures. Stainless steel threaded inserts simplify attachment to printed circuit board.

- Double-Start ACME Thread
- Right Angle Contacts
- High Temperature Housing
- Threaded Inserts
- Environmentally Sealed

How To Order						
Sample Part Number	801-023	-07	M	7-10	P	A
Series	801-023 = PCB Right Angle Receptacle					
Shell Style	-07 = Jam Nut					
Material and Finish	C = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant M = Aluminum / Electroless Nickel RoHS Compliant MT = Aluminum / Nickel-PTFE RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate Z1 = Stainless Steel / Passivated RoHS Compliant					
Shell Size - Insert Arrangement	5-3, 6-1, 6-23, 6-4, 6-6, 6-7, 7-1, 7-25, 7-10, 8-2, 8-28, 8-13, 9-4, 9-210, 9-19, 9-200, 10-2, 10-5, 10-201					
Contact Type	P = Pin S = Socket					
Shell Key Positions (See Table I)	A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. F F = Pos. F					



	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[801-023-07M6-7SA](#) [801-023-07M6-4SA](#) [801-023-07M7-10SA](#) [801-023-07M5-3PA](#) [801-023-07M6-7PA](#) [801-023-07M7-10PA](#) [801-023-07M8-13PA](#) [801-023-07NF6-7SA](#) [801-023-07ZNU5-3PA](#) [801-023-07ZNU5-3SB](#) [801-023-07ZN8-13SA](#) [801-023-07NF7-10PB](#) [801-023-07ZN8-13SB](#) [801-023-07M9-19PC](#) [801-023-07M9-19SA](#) [801-023-07M8-13SA](#) [801-023-07NF7-10PA](#) [801-023-07NF6-7PA](#) [801-023-07M5-3SA](#) [801-023-07M9-19PA](#) [801-023-07ZNU8-13SA](#) [801-023-07Z15-3PA](#) [801-023-07NF7-10PD](#) [801-023-07ZNU7-10SA](#)