

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	28[mm]
Max. Air Flow:	26.8[CFM]
Max. Air Flow:	0.76[m ³ per min]
Max. Static Pressure:	2.52[In H ₂ O]
Max. Static Pressure:	630[Pa]
Fan Speed:	20000[RPM]
Noise:	60[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	10.8[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.66[A]
Input Power:	7.9[W]
Mass:	53[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04028DA-12Q-AA-F0](#)