



Part Number: 2725-2824-BE-01000-A

STYLE	USB2.0 UL2725 28#/1P+24#/2C+AEB		DOCUMENT NO.	VG0942016042901
CONSTRUCTION ITEM		1P		2C
CONDUCTOR	SIZE	28AWG		24AWG
	MATERIAL	TC		TC
	CONSTRUCTION	7/0.12±0.008mm		7/0.20±0.008mm
INSULATION	AVG. THICK	0.22mm		0.24mm
	MIN. THICK	0.15mm		0.17mm
	MATERIAL	HDPE		SR-PVC
	DIAMETER	0.85±0.05mm		1.00±0.05mm
SHIELDED	FILLET SHIELD	-----		
	AL/MYLAR MATERIAL	AL/MYLAR		
	AL/MYLAR CONSTRUCTION	12/0.02mm		
	MYLAR MATERIAL	-----		
	MYLAR CONSTRUCTION	-----		
	DRAIN MATERIAL	TC		
	DRAIN CONSTRUCTION	7/0.12±0.008mm		
	BRAID MATERIAL	ALMg		
BRAID CONSTRUCTION	16/4/0.12±0.008mm		7-8目	
COVERED	AVG. THICK	-----		
	MIN. THICK	-----		
	MATERIAL	-----		
	DIAMETER	-----		
	COLOR	-----		
JACKET	AVG. THICK	0.93mm		
	MIN. THICK	0.79mm		
	MATERIAL	65P UL-PVC ALL raw materials meet rohs standards		
	DIAMETER	4.5±0.15mm		
	COLOR	IV-29# (HALF ATOMIZER)		
MARKING	MARKING NO. 内容(513#)	USB HIGH SPEED CABLE 2.0 REVISION E189529  AWM 2725 28AWG/1PR AND 24AWG/2C 80°C 30V VW-1		
	COLOR	BLACK		
CONSTRUCTION DRAWING & COLOR				
 <p>AL/MYLAR INSULATION CONDUCTOR DRAIN BRAID JACKET</p>			<p>芯线颜色: 1P: WHITE, GREEN 2C: RED, BLACK</p>	
ELECTRICAL CHARACTERISTICS 电气特性				
<p>1. Conductor Resistance: AT 20°C Max: A: 237.25 OHM/KM B: 93.25 OHM/KM                  2. Insulation Resistance: AT 20°C Min: 10M Ω/KM                  3. Dielectric Strength: AC500V 60HZ/分钟</p>				

制作: LYD  
单位: 工程课  
文件编号: VG-SOP-002

审核: 

核准: 

修订日期:  
版次: C0

2016.04.29  
页次: P1