

PART NO. SSS1582F1SSSP-WH(R)		SCALE: NONE		DATE: 02/12/09		APRVD: HM		Limitation of Use: Globtek product are not authorized for use as mission critical components in life support, hazardous environments, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.		Foot Note: Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL, CSA or EN Standards for proper installation instruction.	
REV. A		SIZE A		DATE: 02/12/09		DRAWN: NF		Limitation of Use: Globtek product are not authorized for use as mission critical components in life support, hazardous environments, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.		Foot Note: Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL, CSA or EN Standards for proper installation instruction.	
DWG TITLE: NORTH AMERICAN NON-DETACHABLE RETRACTILE CORDSET		TOLERANCES: DECIMALS ANGULAR +/- .1 MILLIMETERS ANGULAR +/- .005 xxx +/- .013		DATE: 02/12/09		INTBY: GC		Limitation of Use: Globtek product are not authorized for use as mission critical components in life support, hazardous environments, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.		Foot Note: Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL, CSA or EN Standards for proper installation instruction.	
186 Veterans Dr. Northvale, NJ 07647 Tel. 201-784-1000 Fax 201-784-0111 www.globtek.com		ANGULAR +/- .1 MILLIMETERS ANGULAR +/- .005 xxx +/- .013		DATE: 02/12/09		DRAWN: NF		Limitation of Use: Globtek product are not authorized for use as mission critical components in life support, hazardous environments, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.		Foot Note: Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL, CSA or EN Standards for proper installation instruction.	

TABULATION BLOCK			
DASH NO.	PART NO	REV.	DESCRIPTION
			NOTES

WIRE	COLOR	ROJ ± 3 mm
NEUTRAL	WHITE	76
LINE #1	BLACK	76
GROUND	GREEN	76
LINE #2	RED	76


NOTES:
1. CORD AND PLUG MUST BE MARKED WITH APPROVAL SYMBOLS AND/OR FILE NUMBERS.
2. MARKING TO BE PRINTED INTO CABLE JACKET



CONDUCTOR TERMINATION TABLE:

GENERAL SPECIFICATIONS:
RATING: 10A / 300V AC
CABLE TYPE / SIZE: SJT, # 18 AWG, 4 CONDUCTOR
TEMPERATURE RATING: 105° C
CONDUCTOR COLORS: BLACK / WHITE / GREEN / RED
CABLE JACKET COLOR: WHITE (SEE NOTE 2)
LENGTH(D) OF COIL(RETRACTED): 330 ± 20 mm
LENGTH (E): 152 ± 20mm
COIL OUTER DIAMETER: 25 ± 5 mm
END 'A': REMOVE OUTER JACKET (SEE TERMINATION TABLE), ENDS CUT BLUNT
END 'B': REMOVE OUTER JACKET (SEE TERMINATION TABLE), ENDS CUT BLUNT
APPROVALS CABLE: UL, CSA or cUL

PACKING:
BULK PACKED, BUNDLES OF 25.
MAXIMUM SHIPPING CARTON WEIGHT IS 30 KG.



PROPRIETARY INFORMATION: USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.			
REVISION	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE, RFS. 15635, GC	02/12/09	BS