

Specification Sheet

Part Number: 126-00041



Easy and quick insertion ideal for production environment.

Tie "clicks" into place upon final installation signaling installer insertion is complete.

Arrowhead style mount provides low insertion and high extraction force.

1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66, Natural, 100/pkg

Article Number 126-00041

Type T18RWPM

Color Natural (NA)

Quantity Per bag

Product Description Wing design helps stabilize the tie in high vibration applications. One-piece mounting ties offer a complete solution by both bundling cable and simultaneously providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description 1-Piece Cable Tie/Arrowhead Mount with Wings, 4.5"L, 18lb, 0.19 - 0.22" Mtg Hole, PA66, Natural, 100/pkg

Global Part Name T18RWPM-PA66-NA

Minimum Tensile Strength (Imperial) 18.0

Minimum Tensile Strength (Metric) 80.0

Length L (Imperial) 4.5

Length L (Metric) 113.0

Fixation Method Arrowhead

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.1

Width W (Metric) 2.5

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 0.87

Bundle Diameter Max (Metric) 22.2

| | |
|--|--------------|
| Thickness T (Imperial) | 0.043 |
| Thickness T (Metric) | 1.1 |
| Height H (Imperial) | .23 |
| Height H (Metric) | 5.80 |
| Panel Thickness Min (Imperial) | 0.06 |
| Panel Thickness Max (Imperial) | 0.13 |
| Panel Thickness Min (Metric) | 1.52 |
| Panel Thickness Max (Metric) | 3.2 |
| Mounting Hole Diameter D (Imperial) | 0.19 - 0.22 |
| Mounting Hole Diameter D (Metric) | 4.8 - 5.6 mm |
| Mounting Hole Diameter D Min (Imperial) | 0.19 |
| Mounting Hole Diameter D Max (Imperial) | 0.22 |
| Mounting Hole Diameter D Max (Metric) | 5.6 |
| Disc Diameter (Metric) | 13.1 |
| Disc Diameter (Imperial) | 0.5 |

| | |
|--------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| ROHS Compliant | Yes |
| Certification/Specification | UL |
| UL Recognized (US) | Yes |
| UL Listed (US and Canada) | Yes |
| UL Recognized (US and Canada) | Yes |
| UL Listed (US) | Yes |
| Package Quantity (Imperial) | 100 |
| Package Quantity (Metric) | 100 |
| Customs Number | 3926909988 |