

Specification Sheet

Part Number: 156-00017

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.



Outside Serrated Cable Tie & Edge Clip, 5.9" Long, EC21, 1–3 mm Panel, 50lb, PA66HS, Black, 500/pkg

Article Number 156-00017

Type T50SOSEC21

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Short Description Outside Serrated Cable Tie & Edge Clip, 5.9" Long, EC21, 1–3 mm Panel, 50lb, PA66HS, Black, 500/pkg

Global Part Name T50SOSEC21-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 6.0

Length L (Metric) 150

Fixation Method EdgeClip, sideways, assembled, 2 piece

Identification Plate Position none

Releasable Closure No

Variant Outside Serrated

Width W (Imperial) 0.18

Width W (Metric) 4.6

Bundle Diameter Min (Imperial) 0.20

Bundle Diameter Min (Metric) 1.0

Bundle Diameter Max (Imperial) 1.4

Bundle Diameter Max (Metric) 35.0

Thickness T (Imperial) 0.05

Thickness T (Metric)	1.3
Height H (Imperial)	0.05
Height H (Metric)	1.3
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988
Weight (Metric)	1.9
Weight (Imperial)	0.075