

Specification Sheet

Part Number: 156-01340



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.

1-Pc Cable Ties with Pipe Clip, 15-18mm, PA66HIRHS, Black, 500/pkg

Article Number 156-01340

Type T50SMVCOC15-18

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

Short Description 1-Pc Cable Ties with Pipe Clip, 15-18mm, PA66HIRHS, Black, 500/pkg

Global Part Name T50SMVCOC15-18-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 222

Length L (Imperial) 8.3

Length L (Metric) 210.0

Fixation Method Omega Clips

Identification Plate Position none

Width W (Imperial) 0.19

Width W (Metric) 4.7

Bundle Diameter Min (Imperial) 0.08

Bundle Diameter Min (Metric) 2.0

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 50.0

Material Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

| | |
|------------------------------------|--|
| Material Shortcut | PA66HIRHS PA66HS |
| Material Cable Tie | Polyamide 6.6 heat stabilized (PA66HS) |
| Flammability | UL 94 HB |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |