

Specification Sheet

Part Number: CTAM10C2



Suitable for applications with minimal space.

CTAM has 4-way entry design for use in line or at 90° angle to cable run.

CTAM mounts are available in different sizes and materials.

Cable Tie Anchor Mount, .17" Hole Dia, .20" Max Tie Width, PA66, Black, 100/pkg

Article Number 151-31101

Type CTAM1

Color Black (BK)

Quantity Per bag

Product Description Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.

Short Description Cable Tie Anchor Mount, .17" Hole Dia, .20" Max Tie Width, PA66, Black, 100/pkg

Global Part Name CTAM1-PA66-BK

Length L (Imperial) 0.80

Length L (Metric) 20.4

Fixation Method Screw Mounting and Rivet

Width W (Imperial) 0.40

Width W (Metric) 10.2

Cable Ties T18 - T50

Height H (Imperial) 0.20

Height H (Metric) 5.10

Cable Tie Width Max (Imperial) 0.2

Cable Tie Width Max (Metric) 5.0

Mounting Hole Diameter D (Imperial) 0.17

Mounting Hole Diameter D (Metric) 4.3 mm

Mounting Hole Diameter D Max (Metric) 4.3

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988