


Specification Sheet

Part Number: 151-00651



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box

Article Number 151-00651

Type TC6FT6LG

Color Natural (NA)

Quantity Per box

Product Description HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Short Description Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box

Global Part Name TC6FT6LG-PA66HIRHS-NA

Length L (Imperial)	1.5
Length L (Metric)	38.1
Fixation Method	Fir Tree
Width W (Imperial)	0.5
Width W (Metric)	12.0
Height H (Imperial)	1.0
Height H (Metric)	26.60
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.71
Panel Thickness Min (Metric)	0.70
Panel Thickness Max (Metric)	18.0
Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.2

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988