

## Specification Sheet

Part Number: 211-60007



P-Clamps easily guide and locate wire and cables up to 1" in diameter. Designed with a radius edge to prevent chafing and cutting into insulation.

P-Clamp, 0.39" Wide, 0.55" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 100/pkg

**Article Number** 211-60007

**Type** H8P

**Color** Black (BK)

**Quantity Per** bag

**Product Description** HellermannTyton P-Clamps easily guide and locate wires and cables. The clamps are designed with a radius edges to prevent chafing and cutting into insulation. Available sizes up to 1" bundle diameters.

**Short Description** P-Clamp, 0.39" Wide, 0.55" Max Bundle Dia, 0.17" Mounting Hole Dia, PA66HS Black, 100/pkg

**Global Part Name** H8P-PA66HS-BK

<b>Fixation Method</b>	screw-hole
<b>Variant</b>	Closed
<b>Width W (Imperial)</b>	0.39
<b>Width W (Metric)</b>	10.0
<b>Bundle Diameter Max (Imperial)</b>	0.55
<b>Bundle Diameter Max (Metric)</b>	14.0
<b>Nominal Diameter (Imperial)</b>	0.5
<b>Nominal Diameter (Metric)</b>	14.0
<b>Wall Thickness WT (Imperial)</b>	0.059
<b>Wall Thickness WT (Metric)</b>	1.5
<b>Mounting Hole Diameter D (Imperial)</b>	0.17
<b>Mounting Hole Diameter D (Metric)</b>	4.2 mm
<b>Mounting Hole Diameter D Min (Imperial)</b>	0.17
<b>Mounting Hole Diameter D Max (Imperial)</b>	0.17
<b>Mounting Hole Diameter D Max (Metric)</b>	4.2
<b>Mounting Hole Centers (Imperial)</b>	0.59

**Material** Polyamide 6.6 heat stabilized (PA66HS)

**Material Shortcut** PA66HS

**Flammability** UL 94 V-2

**UV Resistant (Yes/No)** No

**Operating Temperature** -40°F to +221°F (-40°C to +105°C)

**Reach Compliant (Article 33)** Yes

**ROHS Compliant** Yes

**Package Quantity (Imperial)** 100

**Package Quantity (Metric)** 100

**Customs Number** 3926909988