

Specification Sheet

Part Number: 151-01634

For use with HellermannTyton T18 - T150 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The high-heat, high-bond adhesive is ideal for outdoor applications, with a static load weight of 2.1 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



High Heat High Bond Acrylic Adh Base, 1.49" x 1.49", Use T18-T150 Tie, PA66HIRHSUV, Black, 250/pkg

Article Number 151-01634

Type MB5A

Color Black (BK)

Quantity Per bag

Product Description MB5A4 adhesive mounts are for use with HellermannTyton T18 - T150 Series cable ties to provide stability when securing bundles. The high-heat, high-bond acrylic adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.

Short Description	High Heat High Bond Acrylic Adh Base, 1.49" x 1.49", Use T18-T150 Tie, PA66HIRHSUV, Black, 250/pkg
Global Part Name	MB5A-PA66HIRHSUV-BK
Length L (Imperial)	1.49
Length L (Metric)	37.7
Fixation Method	Screw Mounting and Adhesive
Width W (Imperial)	1.49
Width W (Metric)	37.7
Cable Ties	T18 - T150
Height H (Imperial)	.28
Height H (Metric)	7.1
Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.9
Mounting Hole Diameter D (Imperial)	0.19
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Diameter D Min (Imperial)	0.19

Mounting Hole Diameter D Max (Imperial) 0.19

Mounting Hole Diameter D Max (Metric) 4.8

Mounting Hole Centers (Imperial) 1

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Adhesive Acrylic foam

Flammability UL 94 HB

Adhesive Operating Temperature -40°F to +176°F (-40°C to +80°C)

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Package Quantity (Imperial) 250

Package Quantity (Metric) 250

Customs Number 3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)