

## Specification Sheet

Part Number: 151-01857



For use with HellermannTyton T18 - T150 or Wide Strap cable ties to provide stability when securing bundles.

The high-heat, high-bond adhesive is ideal for outdoor applications, with a static load weight of 2.1 lb.

Extended adhesive liner is easy to remove quickly.

High Heat High Bond Acrylic Adh Base, 1.5" x 1.5", Use T18-T150 or WideStrap Tie, PA66HIRHSUV, Bk, 100/pkg

**Article Number** 151-01857

**Type** WSMB5AHB

**Color** Black (BK)

**Quantity Per** bag

**Product Description** HellermannTyton's Wide Strap Adhesive Mount pairs with our exclusive line of Wide Strap Cable Ties and is ideal for extreme-duty applications. The mount features 3M™ VHB™ (Very High Bond adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.

**Short Description** High Heat High Bond Acrylic Adh Base, 1.5" x 1.5", Use T18-T150 or WideStrap Tie, PA66HIRHSUV, Bk, 100/pkg

<b>Global Part Name</b>	WSMB5AHB-PA66HIRHSUV-BK
<b>Length L (Imperial)</b>	1.49
<b>Length L (Metric)</b>	37.7
<b>Fixation Method</b>	Adhesive
<b>Width W (Imperial)</b>	1.49
<b>Width W (Metric)</b>	37.7
<b>Cable Ties</b>	T18 - T150
<b>Height H (Imperial)</b>	.30
<b>Height H (Metric)</b>	7.7
<b>Cable Tie Width Max (Imperial)</b>	0.5
<b>Cable Tie Width Max (Metric)</b>	12.7
<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Adhesive</b>	Acrylic foam

<b>Flammability</b>	UL 94 HB
<b>Adhesive Operating Temperature</b>	-40°F to +176°F (-40°C to +80°C)
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988

© 2021 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)